

STREAM

Continuous Filtration System

Effort-Saving • Quick • User-Friendly



Features



Continuous Filtration

1

- ◆ Ensure an unceasing process of large capacity solution.
- ◆ Anchor design allows the maximum suction to the last bit of liquid.



Effort-Saving & User-Friendly

2

- ◆ No need of transferring or pouring solution manually.
- ◆ Completes large volume filtration in one set, no more redundant work.



Chemical Resistance

3

- ◆ Glass and PTFE construction ensures highly chemical resistance.
- ◆ Autoclavable components avoid the possibility of contamination.

Applications

- ◆ Solvent purification
- ◆ Large volume filtration



STREAM

Continuous Filter Holder includes:

- (1) Continuous Filtration Kit
- (2) 300 ml or 1000 ml Filter Holder
- (3) GL45 Filtration Adaptor

Specification

Model	Stream 3	Stream 10
Funnel capacity	300 ml	1000 ml
Filter diameter	47 mm	90 mm
Effective filtration area	13.2 cm ²	45.5 cm ²
Hose barb	ID4 ~ ID8	ID4 ~ ID8
Part	Materia	Materia
Continuous filtration kit	PTFE, silicone	PTFE, silicone
Funnel	Borosilicate glass	Borosilicate glass
Support base	Borosilicate glass	Borosilicate glass
Membrane support	Sintered glass	Sintered glass
Clamp	Aluminum	Aluminum
Filtration adaptor	PP (Autoclavable)	PP (Autoclavable)

Examples

Compatible with

◆ Various GL45 Laboratory Glass Bottle



5L, 10L, 15L, 20L, etc.



Ordering
Information



Stream 3, Continuous Filter Holder (300 ml) 167200-S3

1	Continuous filtration kit for 300 ml glass filter holder	167210-36
2	Glass funnel, 300 ml	167210-03
3	Aluminum clamp, 47 mm	167240-01
4	Sintered glass support base, 47 mm (Including No.8 silicone stopper)	167230-03
5	GL45 filtration adaptor	197000-65

Stream 10, Continuous Filter Holder (1000 ml) 167200-S10

1	Continuous filtration kit for 1000 ml glass filter holder	167210-35
2	Glass funnel, 1000 ml	167210-10
3	Aluminum clamp, 90 mm	167240-02
4	Sintered glass support base, 90 mm (Including No.8 silicone stopper)	167230-11
5	GL45 filtration adaptor	197000-65

167300-11(22)	Rocker 300, Vacuum Pump, AC110V, 60Hz (AC220V, 50Hz)
167400-11(22)	Rocker 400, Vacuum Pump, AC110V, 60Hz (AC220V, 50Hz)
189300-11(22)	Rocker 300C, PTFE Coated Chemical Resistant Vacuum Pump, AC110V, 60Hz (AC220V, 50Hz)
189400-11(22)	Rocker 400C, PTFE Coated Chemical Resistant Vacuum Pump, AC110V, 60Hz (AC220V, 50Hz)
197000-55	Laboratory Glass Bottle, 5000 ml

Rocker Scientific Co., Ltd.

Headquarter

19F.-6, No.206, Guanghua 1st Rd., Lingya Dist.,
Kaohsiung City 802, Taiwan (R.O.C.)
T/ +886-7-227-3358 F/ +886-7-227-3716

Taipei office

11F., No. 402, Sec. 1, Ren'ai Rd., Linkou Dist.,
New Taipei City 244014, Taiwan (R.O.C.)
T/ +886-2-2603-3311 F/ +886-2-2603-6622

Get more information for Rocker

www.rocker.com.tw
export@rocker.com.tw

