

# SF, Stainless Steel Filter Holder



## Features

- New outer spin-lock connection facilitates fast and stable installation without clamp.
- Laser-marked graduation helps accurately sample addition.
- Forceps access points on support base help retrieve membrane easily.
- SS316 funnel offers excellent chemical resistance and can be fast sterilized by flame.

## Specifications

Material	100 ml	300 ml	500 ml
Funnel	SS316	SS316	SS316
Support base	SS316	SS316	SS316
Membrane support	SS316	SS316	SS316
Funnel lid	SS316	SS316	SS316

## Specifications

Funnel capacity	100 ml	300 ml	500 ml
Filter diameter	47 mm	47 mm	47 mm
Effective filtration area	11.6 cm <sup>2</sup>	11.6 cm <sup>2</sup>	11.6 cm <sup>2</sup>
Support pore size	70 µm	70 µm	70 µm

## Ordering Information

### SF 1, Stainless Steel Filter Holder (100 ml) 180100-10

1	Stainless steel funnel, 100 ml	180100-01
2	Stainless steel support screen	180100-31
3	Stainless steel support base	180100-00
4	Silicone stopper (No.8)	167110-16

### SF 3, Stainless Steel Filter Holder (300 ml) 180100-30

1	Stainless steel funnel, 300 ml	180100-03
2	Stainless steel support screen	180100-31
3	Stainless steel support base	180100-00
4	Silicone stopper (No.8)	167110-16

### SF 5, Stainless Steel Filter Holder (500 ml) 180100-50

1	Stainless steel funnel, 500 ml	180100-05
2	Stainless steel support screen	180100-31
3	Stainless steel support base	180100-00
4	Silicone stopper (No.8)	167110-16

### SF, Stainless Steel Lid

100 ml Stainless steel lid	180100-11
300 ml / 500 ml Stainless steel lid	180100-13

